

# Cross-Line Laser Levels

Self-leveling,  
easy-to-read  
**horizontal  
& vertical**  
laser lines

**IP54:** water and dust resistant

**Integrated magnetic 360°  
mounting bracket** with 1/4" and  
5/8" tripod mounting threads



**Projects horizontal  
and vertical lines**  
independently or together  
for various alignments



**Plumb spot lasers**  
to pinpoint overhead locations

## Laser Line Levels

Includes core laser level features plus:

- Additional mounting clamp attachment for use on ceiling grid applications
- Molded hard carrying case included

Cat. No.	Plumb Laser	Laser Color	Accuracy	Overall Length	Overall Height	Overall Width
93LCLS	Yes	Cross-Line: Red, Plumb: Red	±3/32" per 33 ft (±2 mm per 10 m)	2.625" (66.7 mm)	5" (127.0 mm)	5.25" (133.4 mm)

## Laser Line Bubble Levels

- Laser projects distance of up to 75' (22.9 m) indoors
- Crisp laser line and spot projects 1/2" (12.7 mm) above base
- Removable leveling base with pin for centering and thumb screws for adjusting the base
- Three easy to ready vials identify horizontal and cross at 0° level and vertical at 90°
- The strong magnetic base attaches to ferromagnetic surfaces
- High-visibility orange cast aluminum body is easy to see on conduit and jobsites

**NEW**  
Product



Cat. No.	Number of Vials	Type of Vials	Overall Length
<b>NEW</b> LBL100	3	0° Horizontal and Cross, 90° Vertical	7.3" (158 mm)

