

Kits and Accessories

Type P2 Panelboards

Table P2-20 – Standard Enclosures

Box Height Inches	Catalog Number				
	Type 1 Standard Trim			Type 3R	Type 3R/12
	Box	Surface	Flush		
26	B26	S26B	F26B	NR26	WP26
32	B32	S32B	F32B	NR32	WP32
38	B38	S38B	F38B	NR38	WP38
44	B44	S44B	F44B	NR44	WP44
50	B50	S50B	F50B	NR50	WP50
56	B56	S56B	F56B	NR56	WP56
62	B62	S62B	F62B	NR62	WP62
68	B68	S68B	F68B	NR68	WP68
74	B74	S74B	F74B	NR74	WP74

Options For Type 1 Trims

Hinged trim – Replace “B” suffix with “H”

Door-in-door – Replace “B” suffix with “D”

Metal card holder – Replace “B” suffix with “M” on standard trim, add “M” suffix on optional trims

Option For 24” Wide Enclosures with Equal Gutter on Both Sides

24” wide with equal gutter on both sides - Add “24” as prefix

Table P2-21 – Breaker Kits and Accessories

Kit No.	Description	Contents
BBKB32	BL/BQD 6-pole 3” branch breaker kit	Kit contains top barrier, (3) A/C connectors, (1) B connector, hardware
BBKNB32	NGB 6-pole 3” branch breaker kit	Kit contains braker support, interphase barriers, (3) A/C connectors, (1) B-phase connector, hardware
BBKED32	ED 6-pole 3” branch breaker kit	Kit contains breaker support, inter-phase barriers, (3) A/C connectors, (1) B-phase connector, hardware
BBKQ1	QJ branch breaker kit for 2 and 3-pole single mount	Kit to contain all connectors and cover plates necessary to mount both 2 and 3-pole breakers
DFK1	BL, BQD, ED deadfront kit for 1” pole breakers	Center strips 3”, 6”, 9”, 15”, 21” plus mounting hardware
DFFP3	Deadfront filler 3”	3” empty space filler and hardware
DFFP6	Deadfront filler 6”	6” empty space filler and hardware
BNK2	Branch neutral (P2)	Three tier lug with mounting hardware to increase neutral capacity
P2BK1	P2 250A max. Bonding Kit	Bonding strap and hardware
P2BK2	P2 400A max. Bonding Kit	Bonding strap and hardware
P2BK3	P2 600A max. Bonding Kit	Bonding strap and hardware