

- Offered in standard size and mid-size versions to match existing or new wiring devices
- Molded housing provides stability during installation and offers a simple installation practice with one-piece construction and no loose parts
- Available in the 3 popular service combinations: voice, video, & voice/video to meet the most common applications throughout a home
- Decorator strap versions offered to provide a seamless breadth of line and to compliment other decorator installation



Specific connectivity point solutions for today's needs



Options to match common wallplates

Our connectivity point wallplates and inserts match standard wallplate sizes and styles to coordinate perfectly with any new or existing installation.

See page D-12

Shown:
3562



Contractor-friendly

Connectivity points offer contractors solutions at economical price points that most building and remodeling jobs require, yet feature the quality and durability they need.

See page D-13

Shown:
3521-4



Quick & simple installation

One-piece design and construction reduces time on the job, plus there are fewer parts to keep track of and less waste. Available in many common service point configurations.

See page D-13

Shown:
3536-4



Wallplates with connectors

Product description

Standard size
Mid-size
Category 3 RJ11, RJ14, RJ25; coax Type F

Design features

- Telephone jacks for use in Category 3 RJ11, RJ14 or RJ25 applications
- Type F coaxial jack ideal for use with cable, satellite, TVs, DVDs, video applications and outdoor antennas
- 100% computer-tested to assure consistent high quality and reliable performance
- Telephone jacks feature color-notched terminals and wire for easy wiring



1172



3521-4



3535-4



2072



3536-4

Standard size wallplates with connectors

| Description | Color suffix | Catalog no. | |
|-----------------------------------------------------------------------------------------------------|--------------|-------------|---|
| Single coaxial adapter with wallplate, Type F | LA, V, W | □ 1172__ | • |
| Surface mount telephone jack quick mount wallplate, RJ11 or RJ14, 4-conductor, 630A screw terminals | LA, V, W | □ 3521-4__ | • |
| Telephone jack with wallplate, RJ11 or RJ14, 4-conductor, 625B4 screw terminals | LA, V, W | □ 3532-4__ | • |
| Combination coax & telephone jack with wallplate, 4-conductor, screw terminals, Type F | LA, V, W | □ 3535-4__ | • |

cULus Listed to UL1863, file no. E142334; FCC part 68 requirements

Mid-size wallplates with connectors

| Description | Color suffix | Catalog no. | |
|----------------------------------------------------------------------------------------|--------------|-------------|---|
| Single coaxial adapter with wallplate, Type F | A, LA, V, W | □ 2072__ | • |
| Telephone jack with wallplate, RJ11 or RJ14, 4-conductor, 625B4 screw terminals | A, LA, V, W | □ 3533-4__ | • |
| Two telephone jacks with wallplate, RJ11 or RJ14, 4-conductor, 625B3 screw terminals | LA, V, W | □ 3547-4__ | • |
| Combination coax & telephone jack with wallplate, 4-conductor, screw terminals, Type F | LA, W | □ 3536-4__ | • |

cULus Listed to UL1863, file no. E142334; FCC part 68 requirements

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), LA (Light Almond), V (Ivory), W (White)

| | | | |
|----------|--------------|---------|---------|
| A | LA | V | W |
| (Almond) | (Lt. Almond) | (Ivory) | (White) |

Specification information: Please visit www.eaton.com/wiringdevices

Compliances, specifications and availability are subject to change without notice.

RoHS compliant