

## **XTP<sup>®</sup>**


The Marrette<sup>®</sup> XTP<sup>®</sup> is a high quality, twist-on wire connector with a unique spring and cap grip design that sets it apart from the competition.

### **External Cap**

- Made of tough, durable polypropylene and 105°C rated to withstand high installation pressures.
- Posi-Grip<sup>®</sup> surface combines a matte finish with closely-spaced, deep grooves for superior twisting power, even when hands are greasy or damp.
- Deep, wide throat ensures full insulation coverage.
- Threaded entry helps guide large wire bundles into the spring chamber.
- · Colour-coded for quick and easy size selection.

#### **Inner Spring**

- Exclusive Live Action<sup>®</sup> variable volume spring expands to accommodate more wires with less twisting effort, compared to other connectors with a "fixed spring" design.
- Models nos. 329 and 330 have a round spring, while 331, 333 and 335 have a square wire spring construction that gives a positive conductor bite to solid or stranded wires.
- Unique copper-coated spring helps resist corrosion.
- Models nos. 329 and 330 are approved for circuits up to 300 V only. Models nos. 331, 333, 335 and 822 are approved for circuits up to 600 V, and lighting fixtures and signs up to 1000 V.
- For copper conductor only.
- Convenient packaging sized right and job-site ready!









# Wire Connectors

**SP** 

(Սլ

# **XTP<sup>®</sup>**

## **Ordering Information**

Model	Colour	AWG Wire Range									
		22	20	18	16	14	12	10	8		
329	grey	Min.: 1 #22 + 1 #2	20 Max.: 2 #16								
330	blue	Min.: 1 #22 + 1 #2									
331	orange		.0 1110	Min.: 2 #18 Max.:	3 #14						
333	yellow			Min.: 2 #18 Max.:							
335	red	Min.: 2 #14 Max	· 3#10		2						
822*	blue	Min.: 2 #14 Max	1								
Drivers											
TOOL 331	Plastic driver to i	Plastic driver to install Model 331 (included in all packs of 1000 units + )									
TOOL 333	Plastic driver to install Model 333 and 822 (included in all packs of 1000 units + )										
T00L 335	Plastic driver to install Model 335 (included in all packs of 1000 units +)										

.....

Note: Refer to pages A23 to A26 and A28 to A29 for related Wire Combination Reference Guides  $^{\ast}\text{UL}$  not applicable.

## **Packaging Options**

	Cat. No.	Packaging Format	Quantity per Package	Std. Pkg. (Min./Mult.)
329	329P	Propak	100	1,000 Units
	329BP	Bulk Box	1,000	1,000 Units
	329BK	Flip-Pak	10,000	10,000 Units
	330P	Propak	100	1.000 Units
330	330BP	Bulk Box	1.000	1.000 Units
000	330BK	Flip-Pak	10,000	10,000 Units
	004 B	Danasla	100	1.000 Usite
	331P	Propak	100	1,000 Units
	331D	Flip-Pak	500	2,000 Units
331	331KP	Resealable Bag	500	5,000 Units
001	331M	Flip-Pak	1,000	1,000 Units
	331BK	Flip-Pak	10,000	10,000 Units
	331BAR	Barrel	45,000	45,000 Units
	333P	Propak	100	1,000 Units
	333KP	Resealable Bag	500	5,000 Units
າງງ	333D	Flip-Pak	500	500 Units
333	333M	Flip-Pak	1,000	1,000 Units
	333BK	Flip-Pak	10,000	10,000 Units
	333BAR	Barrel	25,000	25,000 Units
	335P	Propak	100	1,000 Units
005	3350	Flip-Pak	200	800 Units
335	335D	Flip-Pak	500	500 Units
	335BK	Flip-Pak	7,000	7,000 Units
	8220	Flip-Pak	200	800 Units
	822D	Flip-Pak	500	500 Units
822	822BK	Flip-Pak	8,000	8,000 Units
	822BAR	Barrel	20.000	20,000 Units



