

M12 FUEL
5-3/8" Circular Saw Kit

2530-21XC (2530-20 Tool-Only)

Specifications:

RPM	3,600
Bevel Capacity	50°
Cut Capacity	1-5/8" at 90°; 1-1/8" at 45°
Arbor	10 mm
Blade Guards	Aluminum
Weight	6.2 lbs



Includes: (1) M12™ REDLITHIUM™ XC4.0 Battery Pack, Circular Saw Blade, Wrench, Charger, Contractor Bag



M12™ High Performance Jig Saw Kit

2445-21 (2445-20 Tool-Only)

Specifications:

SPM	0 – 2,800
Stroke Length	3/4"
Bevel Capacity	45° (Positive Locks at 90° and 45°)
Blade Clamp	QUIK-LOK™ T-Shank
Length / Weight	8.8" / 4.2 lbs



Includes: (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, 10 TPI Wood Cutting T-Shank Jig Saw Blade, Anti-Splintering Insert, Non-Marring Shoe, Charger, Contractor Bag

M12™ Multi-Tool Kit

2426-22, 2426-21 (2426-20 Tool-Only)

Specifications:

Speed Settings	12
OPM	5,000 – 20,000
Universal	Yes
Accessory Adapter	
Length / Weight	10.9" / 2.1 lbs



Includes: 2426-22 (2) M12™ REDLITHIUM™ CP1.5 Battery Packs; 2426-21 (1) M12™ REDLITHIUM™ CP1.5 Battery Pack; **All Kits Include:** Accessory Adapter, Wood Cutting Blade, Sanding Pad, (5) Assorted Sanding Sheets, Charger, Contractor Bag

M12™ Sub-Compact Band Saw Kit

2429-21XC (2429-20 Tool-Only)

Specifications:

SFPM	280
Blade Size	27"
Cut Capacity	1-5/8" x 1-5/8"
Length / Weight	11.0" / 6.7 lbs



Meets OSHA Guarding Requirements. Suitable for One-Handed Use.



Includes: (1) M12™ REDLITHIUM™ XC3.0 Battery Pack, 18 TPI Sub-Compact Portable Band Saw Blade, Charger, Carrying Case

Related Accessories: 48-39-0572 18 TPI Sub-Compact Portable Band Saw Blades (3-Pack); 48-39-0711 12/14 TPI Extreme Metal Sub-Compact Portable Band Saw Blades (3-Pack)



M12 FUEL
HACKZALL® One-Handed Recip Saw Kit

2520-21XC (2520-20 Tool-Only)

Specifications:

SPM	0 – 3,000
Stroke Length	5/8"
Keyless	QUIK-LOK™
Blade Clamp	(Accepts all SAWZALL® Blades)
Length / Weight	13.3" / 4.1 lbs



Includes: (1) M12™ REDLITHIUM™ XC4.0 Battery Pack, HACKZALL® Blade, Charger, Contractor Bag

M12™ HACKZALL® One-Handed Recip Saw Kit

2420-22, 2420-21 (2420-20 Tool-Only)

Specifications:

SPM	0 – 3,000
Stroke Length	1/2"
Keyless	QUIK-LOK™
Blade Clamp	(Accepts all SAWZALL® Blades)
Length / Weight	11.0" / 2.6 lbs



Includes: 2420-22 (2) M12™ REDLITHIUM™ CP1.5 Battery Packs; 2420-21 (1) M12™ REDLITHIUM™ CP1.5 Battery Pack; **All Kits Include:** (2) HACKZALL® Blades, Charger, Contractor Bag

M12 FUEL
3" Compact Cut Off Tool Kit

2522-21XC (2522-20 Tool-Only)

Specifications:

Blade Size	3"
RPM	20,000
Arbor Size	3/8"
Cut Depth	0.64"
Blade Rotation	Reversible
Length / Weight	8.9" / 2.4 lbs



Includes: (1) M12™ REDLITHIUM™ XC4.0 Battery Pack, Dust Accessory Shoe, (3) Accessory Blades (Metal Cut Off, Carbide Abrasive, Diamond Tile), Blade Wrench, Charger, Contractor Bag



M12™ Plastic Pipe Shear Kit

2470-21 (2470-20 Tool-Only)

Specifications:

Cut Capacity	Up to 2" Schedule 80 PVC
Torque	1,900 in-lbs
Blade	3 mm Reinforced Stainless Steel
Length / Weight	14.4" / 4.4 lbs



Includes: (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, Charger, Carrying Case

Related Accessory: 48-44-0405 M12™ Plastic Pipe Shear Blade

M12™ Copper Tubing Cutter Kit

2471-22, 2471-21 (2471-20 Tool-Only)

Specifications:

Cut Capacity	3/8" – 1" (1/2" – 1-1/8" O.D.)
Tubing Type	M, L and K Copper
RPM	500
Length / Weight	14.0" / 3.2 lbs



Includes: 2471-22 (2) M12™ REDLITHIUM™ CP1.5 Battery Packs; 2471-21 (1) M12™ REDLITHIUM™ CP1.5 Battery Pack; **All Kits Include:** Charger, Carrying Case

Related Accessory: 48-38-0010 Copper Cutter Wheel (2-Pack)



M12™ Rotary Tool Kit

2460-21 (2460-20 Tool-Only)

Specifications:

Speed Settings	6
RPM	5,000 – 32,000
Collet	1/8", Universal
Length / Weight	9.5" / 1.3 lbs



Includes: (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, (5) Cutting Wheels, Mandrel, Wrench, Charger, Soft Carrying Case

Related Accessory: 49-94-1500 5 Pc Reinforced Cut-Off Wheels



M12™ Soldering Iron Kit

2488-21 (2488-20 Tool-Only)

Specifications:

Max Temperature	750°F
Heat Output	90 Watts
Heat-Up Time	18 Seconds
Heat Indicator	Yes
Interchangeable Tips	Chisel and Point
Length / Weight	11.6" / 0.9 lbs



Includes: (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, Chisel Tip, Pointed Tip, Charger, Carrying Case

M12™ 600 MCM Cable Cutter Kit

2472-21XC (2472-20 Tool-Only)

Specifications:

Cut Capacity	600 MCM Copper, 750 MCM Aluminum, 1-3/16" Communication Cable
Jaw Opening	1-7/16"
Two-Speed	Yes
Length / Weight	10.5" / 6.7 lbs



Includes: (1) M12™ REDLITHIUM™ XC3.0 Battery Pack, Multi-Voltage Charger, Carrying Case

Related Accessory: 48-44-0410 M12™ 600 MCM Cable Cutter Blade