

Project Name

Location

Prepared By



## SATCO S11424

15.5A19/LED/840/120V/D/4PK

Notes

### General

Status	Active
Watts	15.5
Incandescent Equivalent	100
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	4000
Temperature	Cool White
CRI	80
Lumens	1600
Beam Spread	230
Dimmable	Yes Dimmable
Hours Rated	15000
Lamp Type	A-Type
Technology	LED

### Electrical

Operating Frequency	60 Hz
Dimming Type	Traic

### Physical

MOL	4.57
MOD	2.38
Weight (lb.)	0.14

### Additional Information

Enclosure Rating	Enclosed Rated Lamp
Warranty	3 Yr Limited

### Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
CEC Status	Non-Compliant
RoHS Compliant	Yes