

FirstSurge type 2 surge protective device. Rated 120/240V split phase (Up to 400A) at 50/60Hz. Surge spike capacity 60kA. Special features: less than 1 nanosecond response time, Nema 4X enclosure (indoor - outdoor), 3 stage commercial grade notification, ground reference monitoring (GRM), installs onto any brand load center



| | |
|---------------------------|-------------|
| Mounting type | Surface |
| Phase number | 1 |
| Suitability for operation | Residential |

Electricity

| | |
|--|-------|
| Supply voltage frequency rated value 50/60 Hz | Yes |
| Voltage between phase and Ground (GND) rated value | 120 V |
| Voltage between phase and phase rated value | 240 V |

Model

| | |
|-------------------------------|------------|
| Product brand name | Siemens |
| Product sub brand name | FirstSurge |
| Type of electrical connection | Wired |

Mechanical Design

| | |
|-------------|----------------------|
| Depth [in] | 3 in |
| Height [in] | 8 in |
| Material | CONTACT MANUFACTURER |
| Width [in] | 4 in |

General product approval

last modified:

03/10/2020