SIEMENS

Data sheet

US2:B115H



Siemens Low Voltage Molded Case Circuit Breakers Panelboard Mounting 240V Circuit Breakers - Type BL, 1-Pole, 120VAC are Circuit Protection Molded Case Circuit Breakers. Type: BLH Application: Electrical Distribution Standard: UL 489 Voltage Rating: 120V Amperage Rating: 15A Trip Range: Thermal Magnetic Interrupt Rating: 22 AIC Number Of Poles: 1P

Number of poles	1
Suitability for operation	Electrical Distribution
Electricity	
Continuous current rated value	15 A
Model	
Product brand name	SIEMENS
Type of electrical connection	BOLT-ON
Mechanical Design	
Depth [in]	3 in
Design of the product	BLH
Height [in]	1 in
Width [in]	3 in
General product approval	
Standard	UL 489
last modified:	03/30/2020