

TR26352W Tamper- Resistant Decorator Spec Grade Receptacle, Back & Side Wire, 20A, 125V, White

TR26352W



Tamper-Resistant Decorator Spec Grade
Receptacle, Back & Side Wire, 20amp
125volt, White



features & benefits

- Dual mechanical shutter system to help prevent insertion of foreign objects.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- High impact-resistant nylon face and thermoplastic back body.
- Back and side wire capability
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: white
Type: Receptacles
Number Of Poles: 2
Number Of Wires: 3
Special Features: Tamper-Resistant, Back & Side Wire
Style: Decorator

Listing Agencies/Third Party Information

CSA Standard: Yes
cUL Standard: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121406

Dimensions

Depth U S: 0.65"
Height U S: 3.28"
Width U S: 1.32"

Technical Information

Amps: 20 Amp
NEMA Configuration Number: 5-20R
Volts: 125V
Volts A C: 125
Capacity: Duplex
Grade Type: Specification

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant