



Pass & Seymour

# Wall Plates TradeMaster® Thermoplastic Nylon One & Two Gang

TP1, TP2, TP8, TP82, TP26, TP262, TP13, TP23, TP7, TP720

## Maximum durability in plastic wall plates.


**S**elf-extinguishing nylon construction makes these TradeMaster® wall plates virtually unbreakable. They will not crack if excessive torque is applied to installation screws. They are 3/16" higher and wider than typical plastic wall plates — not enough to be apparent to the eye, but the extra size cuts costs by reducing dry wall rework.



### Features & Benefits

An extra 3/16" width and height than standard size wall plates for more tolerance in covering ragged sheet rock openings.

Molded of rugged, virtually unbreakable self-extinguishing .070 inch thick thermoplastic Nylon 6.



Aesthetically pleasing contour design.







TP26-W, TP2-I, TP8-LA





Pre-installed mounting screws on single gang toggle, duplex receptacle and decorator openings.

### Field Uses/Vertical Markets

- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

## Ordering Information

Description	Catalog Number	Color
<b>TradeMaster Toggle Switch Openings</b>		
<b>One Gang</b> 	TP1-I TP1-W TP1 TP1-GRY TP1-BK TP1-RED TP1-LA	Ivory White Brown Gray Black Red Light Almond
<b>Two Gang</b> 	TP2-I TP2-W TP2 TP2-GRY TP2-BK TP2-RED TP2-LA	Ivory White Brown Gray Black Red Light Almond
<b>TradeMaster Duplex Receptacle Openings</b>		
<b>One Gang</b> 	TP8-I TP8-W TP8 TP8-GRY TP8-BK TP8-RED TP8-LA TP8-BL TP8-OR	Ivory White Brown Gray Black Red Light Almond Blue Orange
<b>Two Gang</b> 	TP82-I TP82-W TP82 TP82-GRY TP82-BK TP82-RED TP82-LA TP82-OR	Ivory White Brown Gray Black Red Light Almond Orange
<b>TradeMaster Decorator Openings</b>		
<b>One Gang</b> 	TP26-I TP26-W TP26 TP26-GRY TP26-BK TP26-RED TP26-LA TP26-BL TP26-OR	Ivory White Brown Gray Black Red Light Almond Blue Orange
<b>Two Gang</b> 	TP262-I TP262-W TP262 TP262-GRY TP262-BK TP262-RED TP262-LA TP262-BL TP262-OR	Ivory White Brown Gray Black Red Light Almond Blue Orange

Description	Catalog Number	Color
<b>TradeMaster Blank Plates — Box Mounted</b>		
<b>One Gang</b> 	TP13-I TP13-W TP13 TP13-GRY TP13-BK TP13-RED TP13-LA	Ivory White Brown Gray Black Red Light Almond
<b>Two Gang</b> 	TP23-I TP23-W TP23 TP23-GRY TP23-BK TP23-LA	Ivory White Brown Gray Black Light Almond
<b>TradeMaster Single Receptacle Openings</b>		
<b>One Gang</b> 	TP7-I TP7-W TP7 TP7-GRY TP7-BK TP7-RED TP7-LA	Ivory White Brown Gray Black Red Light Almond
<b>TradeMaster Power Outlet Receptacle Openings</b>		
<b>One Gang</b> 	TP720-I TP720-W TP720 TP720-GRY TP720-LA	Ivory White Brown Gray Light Almond

For more information on these and other P&S products refer to our Product Guide or visit our web site.

# TradeMaster® Thermoplastic Nylon One & Two Gang



Pass & Seymour

## Technical Specifications

### 3rd Party Compliance

UL Listed, Standard UL514, Cover Plates for Flush Mounted Wiring Devices.  
CSA Certified.

### Performance


Environmental	Chemical-Resistant
Flammability	UL94 V2

### Materials


Plate Material	.070" Nylon 6
Plate Finish	Matte
Screws	Steel, Heads Painted to Match Plate Color

### Warranty

1 Year



Dimensions for  
TradeMaster One Gang



Dimensions for  
TradeMaster Two Gang