

Nail Eater® Extreme



- Improved cutting edge provides 30% longer life span.
- Patented new design for improved cutting and cleaner holes
- Self-feeding screw point draws bit through wood
- Patented pending, cutting angle design- smoother starts, reduced cutting loads
- Made of super tough, heat-treated steel; cuts through nails and provides longer life
- “Shorty” bits - for working in tight places, yet still can go through three abutting 2 x 4s
- See “Bit Extensions” if more length is required (see page 127)
- P.O.P packaged
- Made in the USA

SPECIFICATIONS

NAIL EATER® EXTREME SHORTY

Overall Length	7-5/8" (193.7 mm)
Twist Length	5" (127 mm)
Electrical drill required	All Big Shank, 1/2" drill.

NAIL EATER® EXTREME

Overall Length	18" (457.2 mm)
Twist Length	15" (381 mm)

NAIL EATER® EXTREME SHORTY

CAT. NO.	POP UPC NO.	BULK CAT. NO.	BULK UPC NO.	BULK QTY.	HOLE DIA.		HEX SHANK	
					INCH	MM	INCH	MM
62PTS-5/8	31788	—	—	—	5/8	15.9	7/16	11.1
62PTS-11/16	31790	—	—	—	11/16	17.5	7/16	11.1
62PTS-3/4	31792	62PTS-B-3/4	36640	12	3/4	19.1	7/16	11.1
62PTS-13/16	31794	—	—	—	13/16	20.6	7/16	11.1
62PTS-7/8	31796	62PTS-B-7/8	36642	12	7/8	22.2	7/16	11.1
62PTS-1	31798	62PTS-B-1	36643	12	1	25.4	7/16	11.1
62PTS-1-1/8	30431	—	—	—	1-1/8	28.6	7/16	11.1
62PTS-1-1/4	30433	—	—	—	1-1/4	31.8	7/16	11.1

NAIL EATER® EXTREME

CAT. NO.	POP UPC NO.	BULK CAT. NO.	BULK UPC NO.	BULK QTY.	HOLE DIA.		HEX SHANK	
					INCH	MM	INCH	MM
66PT-1/2	30915	—	—	—	1/2	12.7	5/16	7.9
66PT-5/8	30919	—	—	—	5/8	15.9	7/16	11.1
66PT-11/16	30921	—	—	—	11/16	17.5	7/16	11.1
66PT-3/4	30923	66PT-B-3/4	36659	24	3/4	19.1	7/16	11.1
66PT-13/16	30925	—	—	—	13/16	20.6	7/16	11.1
66PT-7/8	30927	66PT-B-7/8	36662	24	7/8	22.2	7/16	11.1
66PT-15/16	30929	—	—	—	15/16	23.8	7/16	11.1
66PT-1	30931	66PT-B-1	36664	24	1	25.4	7/16	11.1
66PT-1-1/8	30935	—	—	—	1/8	28.6	7/16	11.1
66PT-1-1/4	30937	—	—	—	1-1/4	31.8	7/16	11.1

Nail Eater® Extreme Impact Bits



- Quickly bore through creosoted and salt-treated utility poles
- Resists wear, eats through nails and staples
- Self-feeding screw point draws the bit through the wood
- 7/16" hex shank to fit impact drivers
- Available in 18" overall length
- Made in the USA

NAIL EATER® EXTREME

CAT. NO.	POP UPC NO.	HARDWARE DIAMETER		HOLE DIA. DIAMETER		OVERALL LENGTH		HEX SHANK	
		INCH	MM	INCH	MM	INCH	MM	INCH	MM
37868	37868	9/16	14.3	5/8	15.9	18	457.2	7/16	11.1
37869	37869	11/16	17.5	3/4	19.1	18	457.2	7/16	11.1
37870	37870	13/16	20.6	7/8	22.2	18	457.2	7/16	11.1
37871	37871	15/16	23.8	1	25.4	18	457.2	7/16	11.1