

Eaton PowerXL DG1 variable frequency drive

DG1-357D5FB-C21C

UPC:786685975535

Dimensions:

- **Height:** 17.5 IN
- **Length:** 13 IN
- **Width:** 9 IN

Weight:16 LB

Warranties:

- Eaton Selling Policy 25-000 generally applies with some exceptions. Drive products come with a standard 24 months from date of shipment and 36 months with Eaton certified start up all inclusive coverage parts labor and travel.

Specifications:

- **Brake Chopper:** Brake chopper
- **Display:** LCD (graphical) display
- **Input Voltage:** 230V, 208-240V(-15%, +10%)
- **Keypad:** Included
- **Output Current:** 7.5 A
- **Communication:** EtherNet, RS-485, BACnet MS/TP, Modbus TCP and RTU communication
- **Enclosure:** IP21/type 1 enclosure
- **Frame Size:** FR2
- **Frequency Rating:** 50-60 Hz
- **Horsepower:** 5 hp
- **Material:** Coated board
- **Number Of Slots:** (2) Expansion slots
- **Phase:** Three-phase in, three-phase out
- **Protection:** Internal EMC filter and DC choke
- **Series:** DG1 Series
- **Software:** Active Energy Control, Quick Start Wizard

- **Special Features:** Coated boards
- **Torque Rating:** CT
- **Voltage Rating:** 575 V
- **Wattage:** 3.7 kW

Supporting documents:

- [Product Datasheet - DG1-357D5FB-C21C](#)
- [Eaton Specification Sheet - DG1-357D5FB-C21C](#)

Certifications:

- cUL Listed
- UL Listed
- UL 508C
- EN ISO 13849-1
- EN 62061
- IEC 61508

Product compliance:

- C-Tick Compliant
- CE Marked
- RoHS Compliant
- GoST-R