

Electrical accessory families

Electrical accessories for a variety of new and replacement applications

Arrow Hart has one of the most extensive lines of sign and scoreboard lighting devices in the industry and offers a variety of materials for a wide range of incandescent and fluorescent applications including electrical equipment, harnesses and light strings



Ceiling lampholders

Our ceiling lampholder family includes lampholders made of high-temperature thermoplastic or high-strength insulator porcelain in either pull chain or keyless configurations with or without extra 2-pole, 2-wire or 2-pole, 3-wire outlets.



Fluorescent lampholders

The fluorescent family of lampholders includes recessed double contact, slimline and medium bi-pin lampholder styles in either plunger or stationary styles.



Pigtail lampholders

Primarily for use in electrical equipment, harnesses and light strings, our pigtail lampholders are available in either medium base or miniature base, and include weatherproof rubber or phenolic designs.



Sign & scoreboard lampholders

Arrow Hart's broad selection of sign and scoreboard lampholders includes Attachon designs in medium, intermediate and candelabra bases in a variety of panel mounting options featuring snap-in, screw-in, hook, no hook, and spring-washer models.



Sockets

This family of lampholders includes heater and cleat sockets for use with heater elements, stage lighting and similar applications in Edison, medium, candelabra and miniature bases.



Canopy & circuit control switches

For use in fixtures, appliances, doorways and equipment, this family includes a variety of styles and sizes of push button and pull chain canopy switches and circuit control toggle switches.

Sign & scoreboard lighting

Product description

Attachon lampholders,
660W, 250V/AC; 200W, 250V/AC

Features

- Insulation displacement terminals for stranded wire
- Lay in wire channels, 1/4 turn twist top speeds installation
- One piece terminals and contacts, no rivets or eyelets to loosen due to heat
- Sockets are molded of heat-resistant phenolic
- #732 is weatherproof, suitable for outdoor use
- Intermediate and candelabra bases offer snap-in or screw-in panel mounting options
- Keyed spring washer prevents rotation of socket after installation



732



732-3

Medium base Attachon



Rating		Description	Catalog no.		
W	V/AC				
660	250	Weatherproof phenolic, wire range #14 to #12 AWG, hook mounting	□ 732	•	•
		Weatherproof phenolic, wire range #14 to #12 AWG, no hook mounting	□ 732-1	•	•
		Weatherproof phenolic, wire range #14 to #12 AWG, snap-in mounting	□ 732-3	•	•

For panel cutout dimensional data, see Section Q-Technical Reference

Medium base Attachon with guard



Rating		Description	Catalog no.		
W	V/AC				
200	250	Phenolic socket (732), yellow guard, wire range #18 to #12 AWG, hook mounting	□ 1466Y	•	•

Compliances, specifications and availability are subject to change without notice.



Indicates NAFTA compliant - Page Q-32



RoHS compliant - Page Q-32