



Decorator Standard Grade Receptacles

2-Pole, 3-Wire Grounding
15A, 125V/AC




5-15R


FEATURES

- Tamper Resistant versions provide compliance with 2011 NEC® Article 406.12 that states that all receptacles installed in dwelling units must be tamper resistant. 
- Longer, wider strap provides 40% more contact area to wall board, virtually eliminating floating installations.
- Patented built-in wire stripper for #14 and #12 AWG wire to speed installation.
- Patented built-in wire looper for pre-looping.
- High impact-resistant thermoplastic face and back body eliminates breakage.
- Double-wipe ground contacts ensure long-term ground retention.
- Easy access split circuit break-off tab.
- Tri-combo screws accept Slotted-, Phillips, and Robertson-head tools for installation flexibility.
- Terminal screws backed out and ready for wiring.
- Side wire terminals accept up to #10 AWG solid wire.
- Push-in terminals accept #14 AWG solid wire.

Decorator Tamper Resistant Duplex Receptacles

15A 125V/AC; Side & Push Wire

Description	Color Suffix	Catalog No.	
Tamper Resistant NEMA 5-15R Decorator Duplex Receptacle	A, B, BK, GY, LA, V, W	<input type="checkbox"/> TR1107__	•
Auto Grounding Tamper Resistant NEMA 5-15R Decorator Duplex Receptacle	A, B, BK, GY, LA, V, W	<input type="checkbox"/> TR1107-9__	•


  cULus Listed to UL498, file no. E15058; NOM certified





TR1107-9

Decorator Duplex Receptacles

15A 125V/AC; Side & Push Wire

Description	Color Suffix	Catalog No.	
NEMA 5-15R Decorator Duplex Receptacle	A, B, BK, GY, LA, V, W	<input type="checkbox"/> 1107__	•
Auto Grounding NEMA 5-15R Decorator Duplex Receptacle	A, BK, LA, V, W	<input type="checkbox"/> 1107-9__	•

   Listed to UL498, file no. E15058; CSA certified to C22.2, no. 42; NOM certified



1107

Color Ordering Information: For ordering devices, include Cat. No. followed by the color code: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)

Dimensional Information: B-60

Specification Information: Please visit www.cooperwiringdevices.com

 **NAFTA Compliant:** See page F-21