



TH5110D1006/U

FocusPRO 5000 Premier White® heating and cooling thermostat with standard display

Overview

Honeywell's FocusPRO® 5000 digital thermostat offers the perfect blend of features, performance, energy savings and value. With an easy-to-read digital display, the FocusPRO 5000 prominently displays both room and set temperature.

Features

- Easy-access battery replacement
- Displays available in large or standard screen
- Up to 3H/2C - conventional and heat pump
- Precise comfort control (± 1 F) which maintains consistent comfort
- Dual-powered (battery and/or hardwire)
- 5-Year warranty

Product Specifications

Application	1 Heat/1 Cool Conventional Systems and Heat Pumps with No Auxiliary Heat
Dimensions (in.)	3 7/16 in. high x 4 1/2 in. wide x 1 5/16 in. deep
Dimensions (mm)	86 mm high x 114 mm wide x 33 mm deep
Item Type	Product
Mounting	Horizontal
Electrical Ratings	20 to 30 Vac or 750 mV
Frequency	50 Hz; 60 Hz
Stages	Up to 1 Heat/1 Cool
Operating Humidity Range (% RH)	5 to 90% RH, non-condensing
Switch Positions (System)	HEAT-OFF-COOL-AUTO
Switch Positions (Fan)	AUTO-ON
Sensor Element	Thermistor
Accuracy (F)	± 1 F
Accuracy (C)	± 0.5 C
Color	Premier White®
Switch Type	Relay
Power Method	Dual Powered: Battery or Hardwire
Terminal Designations	R, Rc, C, W (O/B), Y, G
Display	Standard backlit display
Display Size	1.95 sq. in.
Changeover	Auto or Manual Selectable
Setting Temperature Range (F)	Heat: 40 F to 90 F; Cool: 50 F to 99 F

Setting Temperature Range (C)	Heat: 4.5 C to 32 C; Cool: 10 C to 37 C
Cycles per Hour	Heating 1-12 CPH; Cooling 1-6 CPH
Cool Current	1.0 A running
Heat Current	1.0 A running
Fan Current	0.5A running