

Replacement Classic Circuit Breakers

Bolt-On Type BQL Single, Multi-Pole, Duplex™, & Quadplex™

Type BQL ②

- ◆ 10,000 / 22,000 Amperes Interrupting Capacity at 120/240VAC.
- ◆ Captive line screw included (#2 Robertson/Slot).

Product Selection

Table 77. Single and Multi-Pole Bolt-On Classic Replacement Circuit Breakers

Ampere Rating	Wire Size Range (Cu/AL 60°C or 75°C) (AWG)	1-Pole 120/240VAC	1-Pole 120/240VAC	2-Pole 120/240VAC	3-Pole 120/240VAC	3-Pole 120/240VAC
		10kAIC	22kAIC	10kAIC	10kAIC	22kAIC
		Catalogue Number	Catalogue Number	Catalogue Number	Catalogue Number	Catalogue Number
15	#14 - 8	BQL15 ①	HBQL15	BQL215	BQL315	HBQL315
20	#14 - 8	BQL20 ①	HBQL20	BQL220	BQL320	—
25	#14 - 8	BQL25	HBQL25	BQL225	—	—
30	#14 - 8	BQL30	HBQL30	BQL230	BQL330	HBQL330
40	#14 - 4	BQL40	HBQL40	BQL240	BQL340	—
50	#14 - 4	BQL50	HBQL50	BQL250	BQL350	HBQL350
60	#8 - 2/0	BQL60	HBQL60	BQL260	BQL360	HBQL360
70	#8 - 2/0	—	—	BQL270	BQL370	HBQL370
90	#8 - 2/0	—	—	BQL290	BQL390	HBQL390
100	#8 - 2/0	—	—	BQL2100	BQL3100	HBQL3100
125	#8 - 2/0	—	—	BQL2125	—	—
135	#8 - 2/0	—	—	BQL2135	—	—
		Requires One 1-Inch (25.4mm) Space		Requires Two 1-Inch (25.4mm) Spaces		Requires Three 1-Inch (25.4mm) Spaces

Type BQL Duplex™ and Quadplex™ ②

- ◆ 10,000 Amperes Interrupting Capacity at 120/240VAC.
- ◆ Captive line screw included (#2 Robertson/Slot).

Product Selection

Table 78. Type BQL Duplex™ and Quadplex™ Bolt-On Classic Replacement Circuit Breakers

Duplex™		Quadplex™ Independent Trip				Quadplex™ Independent Trip			
Two Single Pole Circuits		Two Single Pole Circuits and One Double Pole Circuit				Two Double Pole Circuits			
120VAC		120VAC		120/240VAC		120/240VAC		120/240VAC	
		Ampere Rating	Ampere Rating	Ampere Rating		Ampere Rating	Ampere Rating		Wire Size Range (Cu/AL 60°C or 75°C) (AWG)
Ampere Rating	Catalogue Number	Outer Left (1 Pole)	Centre (2 Poles)	Outer Right (1 Pole)	Catalogue Number	Outer Left & Right (2 Poles)	Centre (2 Poles)	Catalogue Number	
15-15	BQLT-15 ①	15	15	15	BQLT-15-215	15	15	BQLT-215-215	#14 - 4
20-20	BQLT-20 ①	15	20	15	BQLT-15-220	20	20	BQLT-220-220	#14 - 4
30-30	BQLT-30 ①	15	25	15	BQLT-15-225	15	30	BQLT-215-230	#14 - 4
—	—	15	30	15	BQLT-15-230	15	40	BQLT-215-240	#14 - 4
—	—	15	40	15	BQLT-15-240	—	—	—	#14 - 4
Requires One 1-Inch (25.4mm) Space		Requires Two 1-Inch (25.4mm) Spaces				Requires Two 1-Inch (25.4mm) Spaces			

① Switching duty rated (SWD).

② HACR rated.

③ Internal common trip.