


Type DNPL Duplex™, Independent Quadplex™ and circuit breaker packsType DNPL ^{ab}


- 10,000 A interrupting capacity at 120 Vac, 120/240 Vac, and 240 Vac

Table 12. Duplex and Independent Trip Quadplex plug-in circuit breakers


Duplex 2 single-pole circuits 10 per shelf carton		Quadplex independent trip 2 single-pole circuits and 1 two-pole circuit 5 per shelf carton				Quadplex independent trip 2 two-pole circuits 5 per shelf carton			
120 Vac		120 Vac		120/240 Vac		120 Vac		120/240 Vac	
Ampere rating	Catalogue number	Outer left (single-pole) ampere rating	Centre (two-pole) ampere rating	Outer right (single-pole) ampere rating	Catalogue number	Outer left and right (two-pole) ampere rating	Centre (two-pole) ampere rating	Catalogue number	Wire size range (Cu/Al 60 °C or 75 °C)
15–15	DNPL1515	15	15	15	DNPL151515	15	15	DNPL215215	#14–4 AWG
15–20	DNPL1520	15	20	15	DNPL152015	15	20	DNPL215220	#14–4 AWG
15–30	DNPL1530	15	25	15	DNPL152515	15	30	DNPL215230	#14–4 AWG
20–20	DNPL2020	15	30	15	DNPL153015	15	40	DNPL215240	#14–4 AWG
—	—	15	40	15	DNPL154015	20	20	DNPL220220	#14–4 AWG
—	—	15	50	15	DNPL155015	20	30	DNPL220230	#14–4 AWG



Requires one 1.00 inch (25.4 mm) space



Independent trip requires two 1.00 inch (25.4 mm) spaces



Independent trip requires two 1.00 inch (25.4 mm) spaces

a All Type DNPL Duplex and Quadplex circuit breakers carry listing for HACR applications.

b All 15 and 20 A single-pole are switch-duty rated.

Type BP (circuit breaker packs)

- Single carton packaged
- Represents common household combinations



DNPL2020



DNPL155015



DNPL230230

Table 13. Plug-in circuit breaker house packs

Contents	Catalogue number
(3) DNPL151515, (1) DNPL153015, (1) DNPL154015	BP2
(10) BR115, (3) BR215, (1) BR230, (1) BR240	BP4
(2) DNPL1515, (1) DNPL215215, (1) DNPL152015, (1) DNPL153015, (1) DNPL154015	BP16
(6) DNPL1515, (2) DNPL151515, (1) DNPL153015, (1) DNPL154015	BP18
(1) DNPL1515, (3) DNPL151515, (2) DNPL153015, (1) DNPL154015	BP21
(3) DNPL1515, (3) DNPL151515, (1) DNPL153015, (1) DNPL154015	BP23
(16) BR115, (3) BR215, (1) BR230, (1) BR240	BP24
(14) BR115, (2) BR120, (1) BR230, (1) BR240	BP27
5 of DNPL1515, 1 of DNPL2020, 1 of DNPL153015, 1 of DNPL154015	BP31
(1) BR120, (4) DNPL1515, (1) DNPL151515, (1) DNPL153015, (1) DNPL154015	BP32
(10) BR115, (2) BR120, (1) BR215, (1) BR220, (1) BR230, (1) BR240	BP41
(3) DNPL1515, (1) DNPL153015, (1) DNPL154015, (1) DNPL2020, (1) DNPL1520	BP54