

Electronic Fluorescent

T5

No. of lamps	Primary lamp type	Input volts (V)	Starting method	Order code	Description	Max. case temp. (°C)	Input power ANSI (W)	Ballast factor	Input current (A)	Lamps operated				
										F14T5 F21T5	F24T5	F28T5	F28T5ES	F35T5
2	F21T5	120-277	PS	10476	E221T5PS120-277/N	75	47	1.00	0.40	✓				
	F24T5	120-277	PS	10477	E224T5PS120-277/N	75	46	0.90	0.38		✓			
	F28T5	120-277	PS	60105	E228T5PS120-277/N/BULK	75	60	1.00	0.51	✓		✓	✓	
		347	PS	60102	E228T5PS347/N/BULK	75	61	1.00	0.18	✓		✓	✓	
	F35T5	120-277	PS	10460	E235T5PS120-277/N	75	84	0.90	0.69			✓		✓
		347	PS	10461	E235T5PS347/N	75	77	0.90	0.28			✓		✓

T5HO

No. of lamps	Primary lamp type	Input volts (V)	Starting method	Order code	Description	Max. case temp. (°C)	Input power ANSI (W)	Ballast factor	Input current (A)	Lamps operated			
										F54T5HO	F49T5HO F58T8	F39T5HO	TTL 50 TTL 55
2	F54T5HO	120-277	PS	63025	E254T5HOPS120-277/N/XTRM	90	116	0.99	0.97	✓	✓	✓	✓
		347	PS	63026	E254T5HOPS347/N/XTRM	90	116	1.00	0.33	✓	✓	✓	✓
4	F54T5HO	120-277	PS	63027	E454T5HOPS120-277/N/XTRM	90	232	0.99	1.92	✓	✓	✓	✓
		347	PS	63028	E454T5HOPS347/N/XTRM	90	238	1.00	0.68	✓	✓	✓	✓

T8

No. of lamps	Primary lamp type	Input volts (V)	Starting method	Order code	Description	Max. case temp. (°C)	Input power ANSI (W)	Ballast factor	Input current (A)	Lamps operated				
										F32T8	F30T8ES	F28T8ES	F25T8ES	F17T8 F25T8
1	F32T8	120	IS	31010	E132T8IS120/N	75	28	0.90	0.23	✓	✓	✓	✓	✓
			IS	31037	E132T8IS120/L	75	25	0.78	0.21	✓	✓	✓	✓	✓
			IS	56556	E132T8IS120/L/BULK	75	25	0.78	0.21	✓	✓	✓	✓	✓
		347	IS	56557	E132T8IS347/L/BULK	75	25	0.78	0.07	✓	✓	✓	✓	✓
2	F32T8	120	IS	61113	E232T8IS120/N/AS	75	55	0.87	0.49	✓	✓	✓	✓	✓
			IS	61124	E232T8IS120/N/AS/BULK	75	55	0.87	0.49	✓	✓	✓	✓	✓
			IS	61123	E232T8IS120/L/AS	75	48	0.77	0.45	✓	✓	✓	✓	✓
			IS	61126	E232T8IS120/L/AS/BULK	75	48	0.77	0.45	✓	✓	✓	✓	✓
			IS	60075	E232T8IS120/H/90C	90	74	1.20	0.64	✓	✓	✓	✓	✓
			IS	61128	E232T8IS120-277/N/AS	75	55	0.89	0.46	✓	✓	✓	✓	✓
			IS	61131	E232T8IS120-277/L/AS	75	48	0.77	0.40	✓	✓	✓	✓	✓
			PS	61062	E232T8PS120-277/L/AS/BULK	90	52	0.78	0.43	✓	✓	✓	✓	✓
		347	PS	57031	E232T8PS120-277/H/XTRM	90	75	1.20	0.62	✓	✓	✓	✓	✓
			IS	66150	E232T8IS/MIC/347/N/AS	75	57	0.88	0.19	✓	✓	✓	✓	✓
			IS	66151	E232T8IS/MIC/347/N/AS/BULK	75	57	0.88	0.19	✓	✓	✓	✓	✓
			IS	66152	E232T8IS/MIC/347/N/AS/BULK	75	48	0.78	0.14	✓	✓	✓	✓	✓
			IS	60076	E232T8IS347/H/90C	90	74	1.20	0.21	✓	✓	✓	✓	✓
			PS	62992	E232T8PS347/N/AS/BULK	75	56	0.88	0.16	✓	✓	✓	✓	✓
			PS	62993	E232T8PS347/L/AS/BULK	75	47	0.71	0.14	✓	✓	✓	✓	✓
			PS	59741	E232T8PS347/H/XTRM	90	75	1.20	0.22	✓	✓	✓	✓	✓

70

