## **Renovation Interiors**

## 1 Phase, 3 WIRE, 120/240V


## Features

- For use in home renovations with existing load centers<sup>①</sup>
- Suitable for use in indoor Type 1 Enclosure
- Interior, Flush Cover, and Hardware included
- Adjustable depth
- Incoming lugs: 2/0 #4 AWG
- UL listed





Amp Rating	No. of Spaces	No. of Circuits		Min. Enclosure Size (inches)			Max. Enclosure Size (inches)			Cover Dimensions (inches)	
			Catalog Numbers	L	W	<b>D</b> ②	L	W	D <sup>2</sup>	L	W
100	8	16	RE0816ML1100J	13.00	10.50	3.75	19.00	14.25	6.00	22.00	18.00
100	8	16	RE0816ML1100K	20.00	10.50	3.75	26.00	14.25	6.00	29.00	18.00
125	12	24	RE1224ML1125J	17.00	12.25	3.75	21.00	14.25	6.00	23.00	18.00
125	12	24	RE1224ML1125K	22.00	12.25	3.75	26.00	14.25	6.00	29.00	18.00



① Existing enclosure must mearsure within listed dimensions for the use of the kit.

② Depth of enclosure is measured from finished wall surface