



High-Tension Hacksaw



Klein Tools 12-Inch (30 cm) High-Tension Hacksaw has adjustable blade tension up to 30,000 Pounds Per Square Inch for fast, precise cuts. Includes 12-Inch (305 mm) x 24 Teeth Per Inch bi-metal hack saw blade and 6-Inch (152 mm) x 24 Teeth Per Inch bi-metal reciprocating saw blade. Also has convenient blade storage in handle and soft touch grips.

Specifications

Application:	Alternative 45 Degree Mounting for Flush Cutting	Teeth Per Inch:	24
Blade Length:	12" (30.5 cm)	Overall Length:	16.25" (41.3 cm)
Blade Material:	Bi-Metal	Throat Depth:	24
Weight:	1.5 lb (0.7 kg)		