## **CO1 Series**

100 A 120/240 V; combination with or without breaker

## **Product specifications**


- Conductor range (line and load): 6-1/0 AWG
- Aluminum tunnel type connectors for both load and line sides
- · For overhead installation
- For underground installation, gutter option must be ordered (G)
- · With factory-installed neutral conductor
- Suitable for 120/240 V single-phase service entrance for mobile homes, trailers, temporary services, recreational parks and other commercial and residential locations
- Bottom compartment has provision for 2 pole circuit breaker (max 100 A) 10 Ka breakers (22 kA breaker where indicated HI) Siemens (QP, QPH), Eaton (BR), GE (TQL). Only SQD (CHOM) breakers will fit units with suffix SD.
- Supplied with screw type rings
- Weatherproof Type 3R enclosure
- · Primarily used in: All provinces



				Dimensions (in.)			Weight each	
	Cat. no.	Туре	Description	н	W	D	lb	kg
	4 Jaw							
CO1	CO1	Overhead	Provision for 2 pole 10 kA rated circuit breaker	231/2	81/4	43/8	15	6.8
3 6	CO1-G	Underground	Provision for 2 pole 10 kA rated circuit breaker, complete with gutter	231/2	81/4	43/8	15	6.8
	CO1-5V	Overhead	Provision for 2 pole 10 kA rated circuit breaker, comes with 5th jaw	231/2	81/4	43/8	15	6.8
474	CO1-60	Overhead	Comes complete with 2 pole 60 A 10 kA rated circuit breaker	231/2	81/4	43/8	15	6.8
	CO1-60HI	Overhead	Comes complete with 2 pole 60 A 22 kA rated circuit breaker	23½	81/4	43/8	15	6.8
	CO1-70	Overhead	Comes complete with 2 pole 70 A 10 kA rated circuit breaker	231/2	81/4	43/8	15	6.8
	CO1-100	Overhead	Comes complete with 2 pole 100 A 10 kA rated circuit breaker	231/2	81/4	43/8	15	6.8
	CO1-100G	Underground	Comes complete with 2 pole 100 A 10 kA rated circuit breaker, complete with gutter	23½	81/4	43/8	15	6.8
	CO1-100HI	Overhead	Comes complete with 2 pole 100 A 22 kA rated circuit breaker	231/2	81/4	43/8	15	6.8
	CO1-100HI-G	Underground	Comes complete with 2 pole 100 A 22 kA rated circuit breaker, complete with gutter	231/2	81/4	43/8	15	6.8
	CO1-SD	Overhead	Provision for Square D type QO 2 pole 10 kA rated circuit breaker	23½	81/4	4³⁄8	15	6.8
	CO1-SD-G	Underground	Provision for Square D type QO 2 pole 10 kA rated circuit breaker, complete with gutter	231/2	81/4	4 <del>3</del> /8	15	6.8

 $Note: Some \ local \ utilities \ require \ a \ gutter \ option \ for \ underground \ services. \ Order \ with \ suffix \ -G.$ 

## Diagrams



## **CO1 Multi-gang**

200 A (main lugs), 100 A per position 120/240 V; multi-gang combination with or without breaker

					Dimensions (in.)			Weigh	nt Each
	Cat. no.	Туре	Description	Position	Н	W	D	lb	kg
CO12-100HI	4 Jaw								
	CO12	Overhead	2 Gang, Provision for 2 X 2 pole 10 kA rated circuit breaker	2	23½	16½	43/8	30	13.60
	CO12-100	Overhead	2 Gang, Comes complete with 2 X 2 pole 100 A 10 kA rated circuit breaker	2	23½	16½	4 <del>3</del> /8	30	13.60
	CO12-100-U	Underground	2 Gang with blank compartment, comes complete with 2 x 2 pole 100 A 10 kA rated circuit breaker	2	23½	16½	43/8	30	13.60
	CO12-100HI	Overhead	2 Gang Comes complete with 2 X 2 pole 100 A 22 kA rated circuit breaker	2	23½	16½	43/8	30	13.60
	CO12-100HI-U	Underground	2 Gang with blank compartment, comes complete with 2 x 2 pole 100 A 22 kA rated circuit breaker	2	23 <b>½</b>	16½	43/8	30	13.60
	CO12-SD	Overhead	2 Gang, Provision for 2 x Square D type QO 2 pole 10 kA rated circuit breaker	2	23½	16½	43/8	30	13.60
	CO12-SD-U	Underground	2 Gang with blank compartment, Provision for 2 x Square D type QO 2 pole 10 kA rated circuit breaker	2	23½	16½	43/8	30	13.60
	CO13	Overhead	3 Gang, Provision for 3 X 2 pole 10 kA rated circuit breaker	3	23½	24¾	43/8	45	20.41
	CO13-100	Overhead	3 Gang, Comes complete with 3 X 2 pole 100 A 10 kA rated circuit breaker	3	23 <b>½</b>	24¾	43/8	45	20.41
	CO13-100-U	Underground	3 Gang with blank compartment, comes complete with 3 x 2 pole 100 A 10 kA rated circuit breaker	3	23½	24¾	43/8	45	20.41
	CO13-100HI	Overhead	3 Gang, Comes complete with 3 X 2 pole 100 A 22 kA rated circuit breaker	3	23½	24¾	43/8	45	20.41
	CO13-100HI-U	Underground	3 Gang with blank compartment, comes complete with 3 x 2 pole 100 A 22 kA rated circuit breaker	3	23½	33½	4 <sup>3</sup> / <sub>8</sub>	45	20.41
	CO13-SD	Overhead	3 Gang, Provision for 3 x Square D type QO 2 pole 10 kA rated circuit breaker	3	23½	331/8	43/8	45	20.41
	CO13-SD-U	Underground	3 Gang with blank compartment, Provision for 3 x Square D type QO 2 pole 10 kA rated circuit breaker	3	23½	33 <b>1/8</b>	43/8	45	20.41
	CO14	Overhead	4 Gang, Provision for 4 X 2 pole 10 kA rated circuit breaker	4	23½	33 <b>1/8</b>	43/8	60	27.21
	CO14-100	Overhead	4 Gang, Comes complete with 4 X 2 pole 100 A 10 kA rated circuit breaker	4	23½	33½	43/8	60	27.21
	CO14-100HI	Overhead	4 Gang, Comes complete with 4 X 2 pole 100 A 22 kA rated circuit breaker	4	23½	33 <b>½</b>	43/8	60	27.21
	CO14-100HI-U	Underground	4 Gang with blank compartment, comes complete with 4 x 2 pole 100 A 22 kA rated circuit breaker	4	23½	417/16	43/8	60	27.21
	CO14-SD	Overhead	4 Gang, Provision for 4 x Square D type QO 2 pole 10 kA rated circuit breaker	4	23½	417/16	43/8	60	27.21
	CO14-SD-U	Underground	4 Gang with blank compartment, Provision for 4 x Square D type QO 2pole 10 kA rated circuit breaker	4	23½	411/16	43/8	60	27.21

Note: For underground version, add suffix -U.