Star Teck Extreme Director (STED) Teck cable fittings

01 Install fitting into enclosure

02 Insert cable and tighten (as usual)

03 Rotate fitting to desired angle



01



— 02




03

Warning:

Always ensure that the system is de-energized before performing any installation.

Star Teck Extreme Director (STED) Teck cable fittings











Cat. no.	Hub size (in.)	Gland torque (lbin.)					Throat dia. (min. in.)		
			Range over jacket (in.)		Range over armour (in.)		With armour	Without	Overall
			min.	max.	min.	min.	stop	stop	(in.)
STED050	1/2	450	0.600	0.885	0.520	0.795	0.505	0.617	5.375
STED075	3/4	600	0.860	1.205	0.780	1.125	0.645	0.819	5.875

Specifications: Type HLA. CSA Certified Class I, Division 2; Class II, Groups E, F and G, Class III Enclosure Types 4, 4X; Ex e II, IP66. Type 6 UL listed.

For use with jacketed Teck cable, jacketed corrugated metal-clad cable (ACWU) or metal-clad cable (MC). Aluminum or steel armour.