

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301470081](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Plug with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V, Cord Grip Body Size F4

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family Wiring Devices
 Series [130147](#)
 IP Rating IP67
 NEMA Configuration NEMA L16-30
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
 Product Name Watertite Extreme
 Receptacle Type N/A
 Specialty N/A
 Type Plug
 UPC 78678871234

Physical

Cord Grip Body Size F4 1"
 Flange No
 Flip Lid No
 Gender Male
 Length N/A
 Locking Blade Yes
 Net Weight 290.298/g
 Poles 3-pole/4-wire

Electrical

Cord Type N/A
 Current - Maximum per Contact 30.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 3Ø 480V

Material Info

Engineering Number 28W76



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130147 Series](#)