

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301060107](#)  
**Status:** **Active**  
**Overview:** [Stringlights](#)  
**Description:** Super-Safeway Molded Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0') Lead 10 Sockets with Guards, NEMA 5-15 Plug, Overall Length 30.48m (100.0')

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374

**General**

|                             |                              |
|-----------------------------|------------------------------|
| Product Family              | Portable Lighting            |
| Series                      | <a href="#">130106</a>       |
| NEMA Configuration          | NEMA 5-15                    |
| NEMA Rating                 | Rain Tight                   |
| Outlet                      | None                         |
| Overview                    | <a href="#">Stringlights</a> |
| Product Name                | Super-Safeway                |
| Type                        | String Lights                |
| UPC                         | 78678879886                  |
| <b>Physical</b>             |                              |
| Cord Length - Primary       | 1.52m (5.0')                 |
| Cord Length - Secondary     | 1.52m (5.0')                 |
| Depth                       | 47.625mm (1.875")            |
| Duty                        | Industrial                   |
| Guard Included              | Yes                          |
| Guard Type                  | Steel                        |
| Height                      | 107.95mm (4.250")            |
| Length                      | 30.48m (100.0')              |
| Material - Guard            | #8 Gauge Zinc-plated Steel   |
| Mounting Style              | Stringer                     |
| Packaging Type              | Carton                       |
| Socket Construction         | Rubber Molded                |
| <b>Electrical</b>           |                              |
| Bulb Type                   | Incandescent                 |
| Cord Type - Primary         | 12/3 SOOW                    |
| Lamp Type                   | A21                          |
| Lamp Wattage - Maximum      | 200W                         |
| Lumens                      | 2000                         |
| On/Off Switch               | No                           |
| Voltage (Fixture) - Maximum | 120VAC 60 HZ                 |
| <b>Material Info</b>        |                              |
| Engineering Number          | 323126                       |



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Reviewed

**Search Parts in this Series**

[130106 Series](#)