



15A, 120/277V DECORATOR COMBINATION TWO, NON-GROUNDING/SINGLE-POLE SWITCHES, IVORY

6801 | [Pass & Seymour](#)

FEATURES & BENEFITS

Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.



- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Type: Combination, Double
Number Of Poles: 1
Special Features: Non-Grounding
Style: Decorator

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
UL Listing No: 20
UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): 0.94"

Height (US): 3.28"

Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 15A

Volts: 120/277

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

