

---

## 30 AMP NEMA L1430 FLANGED OUTLET, GRAY

L1430FO | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Flanged Outlet 4wire 30amp 125/250volt Turnlok



- Interior components constructed of high-grade brass material for physical and electrical integrity.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Gray  
Type: Flanged Outlet  
Number Of Wires: 4

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CSA Standard: Yes  
UL Listing No: 498  
UL Standard: Yes  
UN SPSC: 39121403

#### DIMENSIONS

Depth (US): 1.765"  
Diameter (US): 3.12"

#### TECHNICAL INFORMATION

Amps: 30A

NEMA Configuration Number: L1430

Volts: 125/250V

Volts (AC): 125/250

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

