



## TAMPER-RESISTANT SPEC GRADE RECEPTACLES, BACK & SIDE WIRE, 15A, 125V, IVORY

TR62I | [Pass & Seymour](#)

### FEATURES & BENEFITS

Tamper-Resistant Spec Grade Duplex Receptacle Back & Side Wire 15amp 125volt Ivory

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- Dual mechanical shutter system to help prevent insertion of foreign objects.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive brass terminal screws for faster installation.
- Internal screw-pressure-plate back and side wire capability.
- Two back wire holes for additional wiring flexibility.
- Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.
- .032 inch thick brass triple-wipe power contacts.
- Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory

Type: Receptacles

Special Features: Tamper-Resistant,back, side wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes

Federal Spec: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121406

UR: No

#### **DIMENSIONS**

Depth (US): 0.9"

Height (US): 3.281"

Width (US): 1.625"

#### **TECHNICAL INFORMATION**

Amps: 15A

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Specification

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

