



30 AMP NEMA L1930 FLANGED INLET, GRAY

L1930FI | [Pass & Seymour](#)

FEATURES & BENEFITS

Flanged Inlet 4wire 30amp 277/480volt Turnlok



- Interior components constructed of high-grade brass material for physical and electrical integrity.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

SPECIFICATIONS

GENERAL INFO

Color: Gray

Type: Flanged Inlet

Number Of Wires: 4

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: No

UL Listing No: 498

UL Standard: Yes

UN SPSC: 39121403

DIMENSIONS

Depth (US): 1.75"

Diameter (US): 3.12"

TECHNICAL INFORMATION

Amps: 30A

NEMA Configuration Number: L1930

Volts: 277/480V

Volts (AC): 277/480

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

