



INDUSTRIAL EXTRA HEAVY-DUTY SPECIFICATION GRADE SWITCH, LIGHTED WHEN ON, BACK & SIDE WIRE, CLEAR

PS15AC1CPL | Pass & Seymour

FEATURES & BENEFITS

1pole Pilot Lighted Switch, Back & Side Wire, 15amp 120volt, Clear



- External screw-pressure-plate back and side wired. Accepts #14 #10 AWG copper or copper-clad conductors
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- Heavy-duty bumper pads for quiet operation.
- High strength thermoplastic polycarbonate toggle.
- · Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- · Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.
- Auto-ground clip assures positive ground.
- This switch is compatible with incandescent loads only and is not recommended for use with LED or CFL lamps.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

SPECIFICATIONS

GENERAL INFO

Color: Clear Finish: Clear Type: Pilot Lighted Duty: Extra Heavy Duty Number Of Poles: 1

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 111

CSA Standard: Yes Federal Spec: Yes UL Listing No: 20 UL Standard: Yes UN SPSC: 39121507

DIMENSIONS

Depth (US): 1.073" Height (US): 3.281" Width (US): 1.320"

TECHNICAL INFORMATION

Amps: 15A Volts: 120VAC Volts (AC): 120 Grade Type: Industrial

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

