



FLOOR BOX

TM1542BOX | [Pass & Seymour](#)

FEATURES & BENEFITS

Floor Box. 38 cubic inch, with knockouts and Auto/Clamps, three screws for mounting to floor. Gray.



- Hinged door is removable and easily replaceable.
- Durable construction, impact, and scratch resistant PVC construction.
- Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.
- Auto/Clamps and knockouts on both sides of box.
- Meets UL514(c) scrub water exclusion test.
- Threaded device mounting holes.
- Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.
- Ready for low-voltage wiring, drill guides on underside of cover.
- UL and cUL Listed.
- Captive screws on TM1542 Series -- screws will not be lost -- new.
- Made in USA.

SPECIFICATIONS

GENERAL INFO

Product Series: Slater
Component Type: Full Assemblies

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CSA Standard: Yes
CUL Listing No: No
cULus: No
cURus: No

Federal Spec: No
UL Listing No: No
UN SPSC: 39121308
UR: No

DIMENSIONS

Depth (US): 4.0"
Diameter (US): 5.5"

TECHNICAL INFORMATION

Floor Type: Wood

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

