

---

## 20 AMP NEMA L520 OUTLET, GRAY

L520FO | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Flanged Outlet 3wire 20amp 125volt Turnlok



- Interior components constructed of high-grade brass material for physical and electrical integrity.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Gray  
Type: Outlet  
Number Of Wires: 3

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 No. 42  
CSA Listed: Yes  
CSA Standard: Yes  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: Yes  
UL Listing No: 498  
UL Standard: Yes  
UN SPSC: 39121403  
UR: No

## DIMENSIONS

Diameter (US): 2.87"

Length (US): 1.34"

## TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: L520

Volts: 125V

Volts (AC): 125

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

