
30 AMP NEMA L530 - SINGLE RECEPTACLE, YELLOW, CORROSION-RESISTANT

CRL530R | [Pass & Seymour](#)



FEATURES & BENEFITS

Turnlok Receptacle 3wire 30amp 125volt Corrosion Resistant, Yellow

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

SPECIFICATIONS

GENERAL INFO

Color: Yellow

Type: Single Receptacles

Number Of Wires: 3

Special Features: Corrosion-Resistant

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Standard: Yes

CUL Listing No: No

cURus: No

Federal Spec: Yes

UL Listing No: 498

UL Standard: Yes

UN SPSC: 39121403

UR: No

DIMENSIONS

Depth (US): 1.28"

Height (US): 3.28"

Width (US): 1.61"

TECHNICAL INFORMATION

Amps: 30A

NEMA Configuration Number: L530

Volts: 125V

Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

