
20 AMP NEMA L620 INLET, GRAY

L620FI | [Pass & Seymour](#)



FEATURES & BENEFITS

Flanged Inlet 3wire 20amp 250volt Turnlok



- Interior components constructed of high-grade brass material for physical and electrical integrity.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

SPECIFICATIONS

GENERAL INFO

Color: Gray

Type: Inlet

Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: CSA C22.2 No. 42, CSA C22.2 No. 144

CSA Listed: Yes

CSA Standard: Yes

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: 498

UL Standard: Yes

UN SPSC: 39121403

UR: No

DIMENSIONS

Depth (US): 1.65"

Diameter (US): 2.87"

TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: L620

Rating (VAC): 250

Volts: 250

Volts (AC): 250

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

