
20 AMP NEMA L620 OUTLET, GRAY

L620FO | [Pass & Seymour](#)



FEATURES & BENEFITS

Flanged Outlet 3wire 20amp 125volt Turnlok



- Interior components constructed of high-grade brass material for physical and electrical integrity.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

SPECIFICATIONS

GENERAL INFO

Color: Gray
Type: Outlet
Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Standard: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: 498
UL Standard: Yes
UN SPSC: 39121403
UR: No

DIMENSIONS

Depth (US): 1.34"

Diameter (US): 2.87"

TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: L620

Volts: 125V

Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

