



## SINGLE RECEPTACLE OPENINGS, ONE GANG, GRAY, 1.406" OPENING

TP7GRY | [Pass & Seymour](#)

### FEATURES & BENEFITS

Trademaster Plate 1gang 1 Single Receptacle Gray



**PRODUCT**  
ENVIRONMENTAL PROFILE

- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- 1.406" diameter opening
- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.

### SPECIFICATIONS

#### GENERAL INFO

Color: Gray  
Size: Standard  
Type: Single  
Special Features: Unbreakable

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CSA Listed: Yes  
CSA Standard: CSA C22.2 No. 42, CSA C22.2 No. 144  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No

UL Listing No: No  
UN SPSC: 39121704  
UR: No

#### **DIMENSIONS**

Weight: 0.04724

#### **TECHNICAL INFORMATION**

Material: Nylon  
Capacity: 1-gang

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

