



SINGLE RECEPTACLE OPENINGS, ONE GANG, IVORY, 1.406" OPENING

TP71 | [Pass & Seymour](#)

FEATURES & BENEFITS

Trademaster Plate 1gang 1 Single Receptacle Ivory



PRODUCT
ENVIRONMENTAL PROFILE

- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- 1.406" diameter opening
- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Size: Standard
Type: Single
Special Features: Unbreakable

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CSA Standard: Yes
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: No

UN SPSC: 39121704
UR: No

DIMENSIONS

Weight: 0.05967

TECHNICAL INFORMATION

Material: Nylon
Capacity: 1-gang

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

