


---

## POWER OUTLET RECEPTACLE OPENINGS, ONE GANG, WHITE

TP724W | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

One Gang Power Outlet Receptacle Opening, 2.156" hole for 2.125" diameter device - 2 mtg. holes, White Nylon.



**PRODUCT**  
ENVIRONMENTAL PROFILE

- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White  
Size: Standard  
Special Features: Unbreakable

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121704  
UR: No

## DIMENSIONS

Diameter (US): 2.156" Hole

## TECHNICAL INFORMATION

Material: Nylon

Capacity: 1-gang

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

