



15 AMP NEMA L515 FLANGED OUTLET, GRAY

4715SS | [Pass & Seymour](#)

FEATURES & BENEFITS

Turnlok Flanged Outlet 3wire 15amp 125volt Grounding



- Interior components constructed of high-grade brass material for physical and electrical integrity.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

SPECIFICATIONS

GENERAL INFO

Color: Gray
Type: Flanged Inlet
Number Of Wires: 3
Special Features: Grounding

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CSA Standard: Yes
UL Listing No: 498
UL Standard: Yes
UN SPSC: 39121403

DIMENSIONS

Depth (US): 1.374"
Diameter (US): 2.562"

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: L515

Volts: 125V

Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

