



15 AMP NEMA L515 FLANGED INLET, GRAY

4716SS | [Pass & Seymour](#)

FEATURES & BENEFITS

Turnlok Flanged Inlet 3wire 15amp 125volt Grounding



- Interior components constructed of high-grade brass material for physical and electrical integrity.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

SPECIFICATIONS

GENERAL INFO

Color: Gray
Type: Flanged Inlet
Number Of Wires: 3
Special Features: Grounding

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CSA Standard: Yes
UL Listing No: 498
UL Standard: Yes
UN SPSC: 39121403

DIMENSIONS

Depth (US): 1.655"
Diameter (US): 2.562"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: L515
Volts: 125V
Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

