
HOSPITAL GRADE QUAD RECEPTACLES

420HRED | [Pass & Seymour](#)



FEATURES & BENEFITS

Hospital Grade Quad Receptacle 20amp 125volt Red



- Rugged nylon face and body withstands impacts and hard use.
- Built-in wire stripping gauge.
- Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.
- Heavy-duty, phosphor bronze contacts.
- Shielding walls guard against live-circuit-to-ground shorts.
- Split circuit break-off tabs.
- UL and CSA listed.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

SPECIFICATIONS

GENERAL INFO

Color: Red
Type: Quad, Receptacles
Special Features: Split Circuit

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 No. 42
CSA Standard: Yes
Federal Spec: No
UL Listing No: UL498
UL Standard: Yes

UN SPSC: 39121406

DIMENSIONS

Height (US): 4.5"

Width (US): 4.5"

TECHNICAL INFORMATION

Amps: 20A

Volts: 125V

Volts (AC): 125

Capacity: Quad

Grade Type: Hospital

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

