

---

## HOSPITAL GRADE QUAD RECEPTACLE, WHITE

420HW | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Hospital Grade Quad Receptacle 20amp 125volt, White



- Rugged nylon face and body withstands impacts and hard use.
- Built-in wire stripping gauge.
- Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.
- Heavy-duty, phosphor bronze contacts.
- Shielding walls guard against live-circuit-to-ground shorts.
- Split circuit break-off tabs.
- UL and CSA listed.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White

Type: Quad, Receptacles

Special Features: Split Circuit

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.23 14

CSA Standard: Yes

Federal Spec: No

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121406

**DIMENSIONS**

Height (US): 4.5"

Width (US): 4.5"

**TECHNICAL INFORMATION**

Amps: 20A

Volts: 125V

Volts (AC): 125

Capacity: Quad

Grade Type: Hospital

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

