



## COMMERCIAL SPEC GRADE RECEPTACLES, SIDE WIRE, 20A, 250V, WHITE

5850W | [Pass & Seymour](#)

### FEATURES & BENEFITS

Commercial Spec Grade Duplex Receptacle, Side Wire 20amp 250volt, White



**PRODUCT**  
ENVIRONMENTAL PROFILE

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: White

Type: Receptacles

Special Features: Side Wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 No.42

CSA Standard: Yes

cUL Standard: Yes

cURus: No  
Federal Spec: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406  
UR: No

#### **DIMENSIONS**

Depth (US): 0.78"  
Height (US): 3.281"  
Width (US): 1.322"

#### **TECHNICAL INFORMATION**

Amps: 20A  
Volts: 250V  
Volts (AC): 250  
Capacity: Duplex  
Grade Type: Commercial

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

