



HEAVY-DUTY SPEC GRADE SINGLE RECEPTACLE, SIDE WIRE, 20A, 250V, IVORY

58511 | [Pass & Seymour](#)

FEATURES & BENEFITS

Heavy-Duty Spec Grade Single Receptacle, Side Wire 20amp 250volt, Ivory



- Auto-ground clip assures positive ground.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.
- Backed-out tr-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.
- One-piece brass triple-wire power contacts for lasting retention.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Type: Single Receptacles
Duty: Heavy Duty
Special Features: Side Wire

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 No. 42
CSA Standard: Yes
cURus: No
Federal Spec: No
UL Listing No: UL498

UL Standard: Yes
UN SPSC: 39121406
UR: No

DIMENSIONS

Depth (US): 1.08"
Height (US): 3.28"
Width (US): 1.380"

TECHNICAL INFORMATION

Amps: 20A
Volts: 250V
Volts (AC): 250
Capacity: Single
Grade Type: Federal Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

