



CLOCK HANGER RECEPTACLES, RECESSED WITH SMOOTH WALL PLATE, 15A, 125V, IVORY

S37131 | [Pass & Seymour](#)

FEATURES & BENEFITS

Clock Hanger Recessed Receptacle with Smooth Wall Plate 15amp 125volt, Ivory



- Single recessed receptacle.
- Smooth wall plate.

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Type: Clock Hanger
Special Features: Clock Hanger
Style: Decorator, Smooth

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CSA Standard: Yes
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: No
UN SPSC: 39121406
UR: No

DIMENSIONS

Depth (US): 1.878"

Height (US): 4.478"
Width (US): 2.74"

TECHNICAL INFORMATION

Amps: 15A
Volts: 125V
Volts (AC): 125
Grade Type: Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

