



15A, 120/125V COMBINATION SINGLE-POLE SWITCH & SINGLE RECEPTACLE, IVORY

6911 | [Pass & Seymour](#)

FEATURES & BENEFITS

Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.



- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

SPECIFICATIONS

GENERAL INFO

Color: Ivory

Type: Standard

Number Of Poles: 1

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 111

CSA Standard: Yes

UL Listing No: 20, 498

UL Standard: Yes

UN SPSC: 39121406

DIMENSIONS

Depth (US): .94"
Height (US): 3.28"
Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15R
NEMA Rating: Yes
Volts: 120/125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

