
MANUAL CONTROLLERS

7806P | [Pass & Seymour](#)



FEATURES & BENEFITS

NEMA 1 Nylon Enclosure with 1/2inch & 3/4inch Knockouts



High horsepower rating of 20HP. Compact design. Gull-wing shaped brass terminal pressure clamps. Constructed of glass-reinforced thermoplastic. Two-point contact arms. One-piece contact carrier. UL508 and cULus Listing of individual device and assembled device within enclosure. Heavy-duty zinc-plated steel strap. Two brass rivets secure strap to housing. External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals. Oversized silver alloy contacts. 2-3/4 inch hubs (7812-EX and 7813-EX). 2-1/2 inch knockouts on back and 2-1/2 inch -3/4 inch knockouts on top and bottom (7812-P, 7813-P, 7806-P). 2-1/2 inch knockouts on bottom and back (7832 and 7833).

- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

SPECIFICATIONS

GENERAL INFO

Type: NEMA 1 Nylon Enclosure
Knockout Size: 1/2" & 3/4"

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
UL Listing No: No
UN SPSC: 39121507

DIMENSIONS

Weight: 0.46574

BUY AMERICAN ACT COMPLIANCE

Buy American Act Status: Trade Agreement Act Compliant