



## HEAVY-DUTY DECORATOR SPEC GRADE RECEPTACLES, BACK & SIDE WIRE, 15A, 125V, BLACK

26252BK | [Pass & Seymour](#)

### FEATURES & BENEFITS

Heavy-Duty Decorator Spec Grade Duplex Receptacle Back & Side Wire 15amp 125volt Black



- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
  - One-piece, brass, triple-wipe power contacts for lasting retention.
  - Heavy-duty compact design for easier installation and long lasting performance.
  - Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
  - Impact-resistant nylon face.
  - Terminal compartments isolated from each other for positive conductor containment.
  - Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
  - All devices fit standard #26 opening wall plate.
  - Tri-drive terminal and mounting screws.
  - Auto-ground clip assures positive ground
  - For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- 
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: Black  
Type: Receptacles  
Duty: Heavy Duty  
Special Features: Back,Side Wire  
Style: Decorator

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Standard: Yes  
cUL Standard: Yes  
Federal Spec: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406

#### **DIMENSIONS**

Depth (US): 0.833"  
Height (US): 3.281"  
Width (US): 1.322"

#### **TECHNICAL INFORMATION**

Amps: 15A  
Volts: 125V  
Volts (AC): 125  
Capacity: Duplex  
Grade Type: Specification

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

