



HEAVY-DUTY HOSPITAL GRADE COMPACT DESIGN RECEPTACLES, BACK & SIDE WIRE, 15A, 125V, GRAY

8200HGRY | [Pass & Seymour](#)

FEATURES & BENEFITS

Heavy-Duty Hospital Grade Compact Design Duplex Receptacle Back & Side Wire 15amp 125volt Gray



- Impact-resistant nylon face.
- One-piece heat-treated triple-wipe brass power contacts.
- Easily accessible break-off line contact connecting tab for split circuit wiring.
- Corrosion-resistant, zinc-plated steel strap is locked in.
- Internal screw-pressure-plate back wire and side wire line terminals accept #14 – #10 AWG copper or copper-clad conductors.
- High strength thermoplastic back body.
- Back wire holes allow entry of conductor insulation partially into body but not into wiring compartment.
- Auto-ground clip assures positive ground.
- Compact design for easy installation.
- Tri-drive terminal and mounting screws.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

SPECIFICATIONS

GENERAL INFO

Color: Gray
Type: Compact Design,Receptacles
Duty: Heavy Duty
Special Features: Back,Side Wire

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes

Federal Spec: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121406

UR: No

DIMENSIONS

Depth (US): .780"

Height (US): 3.281"

Width (US): 1.322"

TECHNICAL INFORMATION

Amps: 15A

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Hospital

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

