
WIDE SLIDE SERIES DIMMER, IVORY

906831 | [Pass & Seymour](#)



FEATURES & BENEFITS

Slide Dimmer, 600watt Preset 3way, Ivory



- Maximum ratings are for continuous full load.
- Many 1000W models fit standard Decorator plates.
- RFI suppression built in.
- Full-On bypass.
- Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting.
- 600W maximum rated dimmers can be ganged without de-rating.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Product Series: Wide Slide
Type: Incandescent
Number Of Poles: 3-Way

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39121502

UR: No

DIMENSIONS

Depth (US): 1.469"

Height (US): 4.25"

Width (US): 1.688"

TECHNICAL INFORMATION

Watts: 600

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

