
15A, 125V EXTRA-HARD USE SPEC-GRADE PLUG, WHITE FACE

PS5266X | [Pass & Seymour](#)



FEATURES & BENEFITS

Straight Blade Plug 2pole 3wire 15amp 125v



PRODUCT
ENVIRONMENTAL PROFILE

- Unit arrives completely ready-to-wire, cuts installation time significantly.
- Nylon housing provides impact and chemical resistance.
- Rugged two-piece cord grip provides more uniform cord retention.
- Internal dust shield keeps terminals free of contaminants.
- Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White, Black

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 No.42
CSA Standard: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121402

DIMENSIONS

Depth (US): 1.752"

Height (US): 1.516"
Width (US): 1.516"

TECHNICAL INFORMATION

NEMA Configuration Number: 5-15P
Volts (AC): 125
Grade Type: Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

